

HMP155 Humidity and Temperature Probe

(*) Note! If warmed probe is chosen and additional temperature sensor is not used output signal for Ch1 must be 'None' and for Ch2 only Td, Tdf or x output can be selected.

Accessories and spares		
Filters	Sintered Teflon filter	219452SP
	Membrane filter	230727SP
Cables	Cable 0.8 m 8-pin M12	272226
	Cable 3.5 m 8-pin M12	220496
	Cable 5 m 8-pin M12	223283
	Cable 10 m 8-pin M12	220497
	Cable 30 m 8-pin M12	220498
	USB-M12 service cable	221040
Radiation shield	Large shield (suitable for HMP155 with additional T-probe)	DTR13
	Compact shield (suitable for HMP155)	DTR503
	Small shield (suitable for additional T-probe)	DTR502
Probe mounting accessories	Additional T-probe installation adapter for DTR13	221069
	Additional T-probe installation adapter for DTR502	221072



Calibration accessory	HMP155 and additional T-probe installation adapter for Stevenson screen	221321
	MI70 measurement indicator	MI70
	MI70 connection cable	221801
	HMK15 humidity calibrator (saturated salt solutions)	HMK15
Others	HMK15 adapter fitting for 12-mm probes	218377SP
	HMP155 connector cover for protection in wet environment	DRW236638
	Protection set for calibration buttons: protective cover, 2 O-rings and protective plug	221318