



# gentec-e)

# QE12LP-H-MB-D0

Pyroelectric detector for laser energy measurement up to 0.85 J.



### PRODUCT FAMILY KEY FEATURES

## MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

#### LOW NOISE LEVEL

0.7 µJ for the MB coating

#### **QED ATTENUATOR AVAILABLE**

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read mo

### HIGH REPETITION RATE OPTIONS

- QE12HR-MB: 1 000 Hz
- QE12HR-MT: 10 000 Hz

#### TEST TARGET INCLUDED

With the MB models

#### SMART INTERFACE

Containing all the calibration data

### COMPATIBLE STAND

STAND-D-233

# **SPECIFICATIONS**

Spectral range <sup>1</sup>	0.193 - 20 µm
Typical rise time	550 µs
Repeatability	<0.5%
Maximum repetition frequency <sup>2</sup>	300 Hz
Maximum measurable energy <sup>3</sup>	0.85 J
Noise equivalent energy <sup>4</sup>	0.7 µЈ
Maximum pulse width	400 µs
Energy calibration uncertainty	±3 %

3. At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.

4. Nominal value. Actual value depends on electrical noise in the measurement system.

### DAMAGE THRESHOLDS

Maximum average power density <sup>1</sup>	10 W/cm <sup>2</sup>
Maximum energy density <sup>2</sup>	0.6 J/cm²
Maximum power	5 W
1. May vary with wavelength and average power.	

2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

#### PHYSICAL CHARACTERISTICS

Cool	

Cooling	Convection (heatsink)
Aperture width	12 mm
Aperture height	12 mm
Absorber	МВ
Dimensions	36H x 36W x 33D mm





200528

203250

202720

# ORDERING INFORMATION

QE12LP-H-MB-D0

QE12LP-H-MB-INE-D0

QE12LP-H-MB-IDR-D0

QE12LP-H-MB-INT-D0

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

# INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us