



gentec-e)

QE25SP-H-MT-D0

Pyroelectric detector for laser energy measurement up to 3.0 J.



PRODUCT FAMILY KEY FEATURES

MODULAR CONCEPT

Increase the power capability of your detector: 2 different cooling modules

LOW NOISE LEVEL

2 µJ for the MB coating

QED ATTENUATOR AVAILABLE

Measure up to 5X higher energies. Available with optional calibration, all wavelengths between 532 & 1064 nm, or single wavelength. Read mo

HIGH REPETITION RATE OPTIONS

- QE25HR-MB: 1 000 Hz
- QE25HR-MT: 10 000 Hz

TEST TARGET INCLUDED

With the MB models

SMART INTERFACE

Containing all the calibration data

COMPATIBLE STAND

STAND-D-233

SPECIFICATIONS

Spectral range ¹	0.193 - 20 μm
Typical rise time	20 µs
Repeatability	<0.5%
Maximum repetition frequency ²	6000 Hz
Maximum measurable energy ³	3 J
Noise equivalent energy ⁴	2 µJ
Maximum pulse width	10 µs
Energy calibration uncertainty	±3 %

May be limited by the display or PC interface. Please refer to the corresponding user mar
At 1064 nm, 7 ns, 10 Hz. Increasing pulse width increases maximum measurable energy.

4. Nominal value. Actual value depends on electrical noise in the measurement system.

DAMAGE THRESHOLDS

Maximum average power density ¹	10 W/cm ²
Maximum energy density ²	0.5 J/cm ²
Maximum power	10 W
1. May vary with wavelength and average power.	

2. At 1064 nm, 7 ns, 10 Hz. May vary with wavelength and pulse width.

PHYSICAL CHARACTERISTICS

Cool	

Weight

Cooling	Convection (heatsink)
Aperture width	25 mm
Aperture height	25 mm
Absorber	MT
Dimensions	50H x 50W x 53D mm
Weight	0.193 kg





Instrument Expert Original factory packaging www.dorgean.com

ORDERING INFORMATION

QE25SP-H-MT-D0

QE25SP-H-MT-INT-D0

200461 202387

Specifications are subject to change without notice. Refer to the user manual for complete specifications.

INTERESTED IN THIS PRODUCT?

GET A QUOTE

Find your local sales representative at gentec-eo.com/contact-us